Hearing Helper® Personal FM Transmitter, Model PFM T31

Description:

The PFM T31 transmitter will broadcast the speaker's voice directly to the ears of individuals equipped with a PFM R31 or PFM R32 receiver. Field tuneable up to 10 channels, the PFM T31 will operate up to 150 feet—ideal for large classroom environments.

Each PFMT31 features a microphone mute switch. The speaker can turn this on and off conveniently when he or she desires private conversation, or, wants to eliminate the transmission of unwanted sound to the rest of the group (i.e. writing on a chalkboard, shuffling papers).

Applications:

Classrooms
Job Consultation
Job Training
Tours
Group Meetings

PFM T31 FM Transmitter:

Dimensions:	3-5/8" L x 2-3/8" W x 7/8" H (92.1 mm x 60.3 mm x 22.2 mm)	On/Off Switch
Weight:	4.4 oz (125 g) with battery	
Color:	Royal blue, shatter-resistant polypropylene	Mic Off ▲ On
Battery Type:	Two (2) AA 1.5 V non-rechargeable Alkaline batteries	
	(BAT 001), 70 mA nominal current drain, 12 hours approx. life	Williams Sound FM
	(OR) Two (2) AA 1.5 V NiMH rechargeable batteries (BAT 026),	
	70 mA nominal current drain, 10 hours per charge approx.,	Mic Jack Mic Mute Switch
	recharges in 14-16 hours, uses CHG 200 Charger	T21 Tam
Operating Freq's:	Selectable, 10 channels, 72.1-75.9 MHz, internal DIP switch	Т31 Тор
Stability:	+ .005%, frequency synthesized, crystal reference, PLL	
Modulation:	Wide-band FM, 75 kHz, 75 µS pre-emphasis	
RF Output:	8000 μV/m at 30 m, max., 40 mW typical	
FCC ID:	CNM T30	Williams Sound
Freq Response:	100 to 10 kHz, + 3 dB at 1% max. THD	
Signal-to-Noise Ratio:	55-60 dB, with R31 or R32 Receiver	Hearing Helper*
Auto Gain Control:	40 dB range, 30 mV threshold	
Transmit Antenna:	Integral with 39" microphone cord	
Microphone:	Omnidirectional condenser, Lavalier-type, 39" cord,	
	3.5 mm mono phone plug (MIC 081)	
Controls:	On/Off switch, slide-type	
	Mute switch, slide-type	
Mic Connector:	3.5 mm mono phone jack	
Warranty:	5 years, parts and labor (90 days on accessories)	

T31 Front

NOTE: SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE!



Hearing Helper® Personal FM Transmitter, Model PFM T31

Bid Specs:

Not Currently Available

Contact:

United States and Mexico

Williams Sound Corp. 10321 W. 70th Street Eden Prairie, MN 55344-3446 Ph: 800-328-6190 / 952-943-2252 / FAX: 952-943-2174 Web: www.williamssound.com Email: info@williamssound.com

Canada

Thorvin Electronics 2861 Sherwood Heights Dr. Units 36-37 Oakville, ON L6J-7K1 Canada Ph: 800-323-6634 / 905-829-3040 / FAX: 905-829-4196 Web: www.thorvinelectronics.com

South America

DPTech SIA Trecho 3/4 Lote 335 2°. Andar 71200-030 Brasília, DF BRAZIL Ph: (5561) 361-1384 Fax: (5561) 361-0948 Web: www.dptech.com.br Email: ws@dptech.com.br

Europe and Asia

International Sales Department Williams Sound Corp. 10321 W. 70th Street Eden Prairie, MN 55344 USA Phone: +1 651 493 2578 or +1 952 943 2252 Fax: +1 952 943 2174 Email: doreeni@williamssound.com Web: www.williamssound.com

